# **ASSA ABLOY PIN Horizontal**



## **Tootekirjeldus**

ASSA ABLOY PIN is a stand-alone battery driven code locker lock.

Stand-Alone means that the lock can be used, programmed and deployed without any software or programming devices.

#### Area of use:

• The lock is designed for usage in dry areas, but can be used in wet area applications together with a rubber gasket.

#### **Characteristic:**

- The lock can be retrofitted by utilising the existing hole foot-print/fixings with just an extra hole for the upper screw.
- The lock can be mounted in both vertical and horizontal position.
- The lock is available in 2 barrel lengths. For assembly on doors with 1-15 mm door thickness and for assembly on doors with 15-23 mm door thickness.
- The lock has sound and light feedback to improve user experience.
- The lock has 3 code levels: User Code (4 digits), Janitor / Staff Code (6 digits) and Master Code (8 digits)
- The lock has a USB connection to be able to supply the lock with emergency power for access in case of depleted batteries.

- Suitable for use with ASSA ABLOY standard cams.
- Built in torque-overload protected clutch function in handle.

### **Functions:**

The lock works in 2 different modes

- Private Mode The locked is open with the same pre-programmed codes.
- Public Mode The lock can be locked with any one time code. Once unlocked the lock is free for input of new user code.

Additional functionality can be easily added/deleted using standard programming.

The lock comes with variable time opening, meaning the lock automatically unlocks after a pre-set period of time.

The lock comes with a time-delay function, which is activated when the wrong code is entered repeatedly.

TOOTENIMETUS	SOODUS	HIND
$\begin{array}{l} \begin{array}{l} D\text{-}D\text{»}D\mu D^{o}\tilde{N},\tilde{N} \in D^{3}\!\!\!/ D^{1}\!\!\!/ 2\tilde{N} \cdot D^{1} \ D \cdot D^{o}D^{1}\!\!\!/ D^{3}\!\!\!/ D^{o} \ D \cdot D^{o}\tilde{N} \cdot \tilde{N}^{\bullet} \ \tilde{N}^{\bullet}D^{o}D^{o}\tilde{N},, \tilde{N}^{\ddagger}_{+}D^{}_{+}D^{o}D^{3}\!\!\!/ D^{2} \\ \text{ASSA ABLOY PIN } (D\text{»}D\mu D^{2}\tilde{N} \cdot D^{1} \ D^{3}D^{3}\!\!\!\!/ \tilde{N} \in D^{}_{+}D^{} \partial^{3}\!\!\!/ D^{1}\!\!\!/ 2\tilde{N}, D^{o}D^{o}\tilde{N}, \tilde{N}^{\bullet}D^{\bullet}D^{1}\!\!\!/ \tilde{N} \cdot D^{1}, \\ D^{o}D^{3}\!\!\!\!/ \tilde{N} \in D^{3}\!\!\!\!/ \tilde{N}, D^{o}D^{}_{+}D^{}_{-}D^{} \partial^{}_{-}D^{}_{-}D^{}_{-}D^{\bullet}D^{3}\!\!\!/ \tilde{N} \cdot D^{\bullet}D^{\bullet}_{-}D^{\bullet}$		124.34 €
$\begin{array}{l} D\text{-}D\text{»}D\mu D^{o}\tilde{N},\tilde{N} \\led{\in} D^{3}\!\!\!/4D^{1}\!\!\!/2D^{1}\!\!\!/2\tilde{N} \\led{\in} D^{1}D^{o}D^{1}\!\!\!/4D^{3}\!\!\!/4D^{o}D^{o}D^{o}\tilde{N},\tilde{N}^{*}D^{o}D^{o}\tilde{N},\tilde{N}^{*}D^{o}D^{3}\!\!\!/4D^{2}\\ ASSA\ ABLOY\ PIN\ (D\text{»}D\mu D^{2}\tilde{N} \\led{\in} D^{3}D^{3}\!\!\!/4\tilde{N} \\led{\in} D^{3}D^{3}\!\!\!/4D^{1}\!\!\!/2\tilde{N},D^{o}D^{o}\tilde{N},\tilde{N}^{*}D^{1}D^{0}D^{3}\!\!\!/4D^{1}\!\!\!/2\tilde{N},D^{o}D^{o}\tilde{N},\tilde{N}^{*}D^{0}D^{0}D^{3}\!\!\!/4D^{1}\!\!\!/2\tilde{N},D^{o}D^{o}D^{o}\tilde{N},\tilde{N}^{*}D^{0}D^{0}D^{0}D^{0}D^{0}D^{0}D^{0}D^{0$		124.34 €
$\begin{array}{l} \begin{array}{l} D\text{-}D\text{»}D\mu D^{o}\tilde{N},\tilde{N} \\led{\in} D^{3}\!\!\!/4D^{1}\!\!\!/2D^{1}\!\!\!/2\tilde{N} \\led{\in} D^{1}D^{o}D^{1}\!\!\!/4D^{3}\!\!\!/4D^{o}D^{o}D^{o}D^{o}\tilde{N},\tilde{N}^{\dagger}_{1}D_{1}D^{o}D^{3}\!\!\!/4D^{2}\\ ASSA\ ABLOY\ PIN\ (D_{c}^{c}\tilde{N}\\led{\in} D^{o}D^{2}\tilde{N} \\led{\in} D^{1}D^{3}\!\!\!/4\tilde{N}\\led{\in} D^{3}\!\!\!/4\tilde{N},D^{o}D^{o}D^{o}D^{o}D^{o}D^{o}D^{o}D^{o}$		124.34 €
$\begin{array}{l} \begin{array}{l} D\text{-}D\text{»}D\mu D^{o}\tilde{N},\tilde{N} \\led{\in} D^{3}\!\!\!/4D^{1}\!\!\!/2D^{1}\!\!\!/2\tilde{N} \\led{\in} D^{1}D^{o}D^{1}\!\!\!/4D^{3}\!\!\!/4D^{o}D^{o}D^{o}D^{o}\tilde{N},\tilde{N}^{\dagger}_{1}D_{1}D^{o}D^{3}\!\!\!/4D^{2}\\ ASSA\ ABLOY\ PIN\ (D_{c}^{c}\tilde{N}\\led{\in} D^{o}D^{2}\tilde{N} \\led{\in} D^{1}D^{3}\!\!\!/4\tilde{N}\\led{\in} D_{1}^{3}D^{3}\!\!\!/4\tilde{N}\\led{\in} D_{2}^{3}D^{3}\!\!\!/4\tilde{D}^{1}\!\!\!/2\tilde{N},\tilde{D}^{o}D^{o}\tilde{N},\tilde{N}^{\dagger}D^{1}D^{0}D^{3}\!\!\!/4D^{1}\!\!\!/2\tilde{N},\tilde{D}^{o}D^{o}\tilde{N},\tilde{N}^{\dagger}D^{0}D^{0}D^{0}D^{0}D^{0}D^{0}D^{0}D^{0$		124.34 €



